

Uncontrolled document as of September 27, 2008. Refer to website for up to date specifications.

LIGHTS 1900 MityLite



MityLite™ 1900 Flashlight

Unlike conventional flashlights that have a yellowish beam, the MityLite 1900 flashlight uses a hi-intensity Xenon lamp that produces a powerful, bright beam. Use this compact flashlight to cut through thick smoke, fog, and dust. It is submersible and comes with a twist-on shroud. The 1900 is ideal for any situation. Powered by 2 AAA alkaline cells.



Minimum Pack 6 ea.
Packaged Weight: 2.4 oz.


NSN #6230-01-345-6314

MityLite™ 1900 Flashlight Configurations

Cat. #	Description
1900	MityLite™ 1900 Flashlight (Carded)
1900T	MityLite™ 1900 Flashlight (Clear Gift Tube)
1950C	MityLite™ 1950 Mini System
1980C	MityLite™ 1900 Knife/Lite Combo
1900M	MityLite™ 1900 Flashlight Merchandiser Display



Submersible



MityLite™ 1900 Flashlight Specifications

Light Source	Tested Lumen Value	Tested Lux Value (@ 1 meter)
Xenon	7.0	1200

Batteries	Battery Burn Time	Battery Pack/Charging Time
2 AAA Alkaline (Included)	2 hrs.	N/A

Watts	Voltage
1.1	3

Length	Weight w/Batteries	Weight w/o Batteries
4.09" (10.4 cm)	1.6 oz. (0.05 kg)	0.75 oz. (0.02 kg)

MityLite™ 1900 Flashlight Approvals

Class I, Div. 2; Gp ABCD, T3C; Class II; Div. 2; Gp G.

Ex ib e IIC T4 IP67 IEC Ex TSA 06.0021X

Class I, Div. 1, GP C,D, T3C CONFORMS TO STD UL 783

MityLite™ 1900 Flashlight Accessories

Cat. #	Description	Sug. Retail
1904	MityLite™ 1900 Lamp Module	US\$5.35
720	Helmet Light Holder	US\$16.50
721	Helmet Light Holder	US\$16.50

Pelican™ Products, Inc.

23215 Early Avenue • Torrance, CA 90505 • Phone: (310) 326-4700 • (800) 473-5422 • Fax: (310) 326-3311
e-mail: sales@pelican.com • www.pelican.com