

# WACKER SilGel® 611 A/B

## SILICONE GEL

### Product description

WACKER SilGel® 611 A/B is a pourable, additioncuring, RTV-2 silicone rubber that vulcanizes at room temperature to a soft silicone gel.

WACKER SilGel® 611 A/B is a white colored modification of WACKER SilGel® 612 with higher hardness and reactivity.

### Special features

- two-part, 1 : 1 mixing ratio
- low viscosity
- rapid cure
- low hardness (silicone gel)

### Application

- encapsulation of electronic components

### Processing

#### Caution:

Only components A and B with the same lot number may be processed together!

To ensure homogeneity of the material, the components must be stirred thoroughly before they are removed or processed in their containers, in order to uniformly disperse any filler that might have settled during storage.

#### Surface preparation

All surfaces must be clean and free of contaminants that will inhibit the cure of WACKER SilGel® 611 A/B. Examples of inhibiting contaminants are sulfur containing materials, plasticizers, urethanes, amine containing materials and organometallic compounds – especially organotin compounds. If a substrate's ability to inhibit cure is unknown, a small scale test should be run to determine compatibility.

#### Mixing

Component B of WACKER SilGel® 611 A/B contains the platinum catalyst, component A the crosslinker.

Even traces of the platinum catalyst may cause gelling of the component containing the crosslinker. Therefore tools (spatula, stirrers, etc.) used for handling the platinum-containing component or the catalyzed compound must not come into contact with this component.

The two components should be thoroughly mixed at a 1 : 1 ratio by weight or volume.

To eliminate any air introduced during dispensing or trapped under components or devices a vacuum encapsulation is recommended.

#### Curing:

Curing time of addition curing silicone rubber is highly dependent on temperature, size and heat sink properties of the component being potted.

The reactivity can be adjusted within wide limits by adding Catalyst EP or Inhibitor PT 88 to suit the processing requirements of the particular application. Catalyst EP increases the reactivity, i. e., pot life and curing time are reduced.

Inhibitor PT 88 is a pot life extender and prolongs pot life and curing time.

Further information is given in our leaflet "Catalyst EP/Inhibitor PT88".

We recommend running preliminary tests to optimize conditions for the particular application.

Comprehensive processing instructions are given in our leaflet "Wacker RTV-2 Silicone Rubber - Processing".

Temperature	Curing time,
23 °C	6 h
70 °C	60 min
120 °C	10 min

### Storage

The 'Best use before end' date of each batch is shown on the product label.

Storage beyond the date specified on the label does not necessarily mean that the product is no longer usable. In this case however, the properties required for the intended use must be checked for quality

assurance reasons.

require special handling precautions. General industrial hygiene regulations should be observed.

### Safety notes

According to the latest findings WACKER SiGel® 611 A/B being an addition-curing silicone rubber contains neither toxic nor aggressive substances which might

Comprehensive instructions are given in the corresponding Material Safety Data Sheets. They are available on request from WACKER subsidiaries or may be printed via WACKER web site <http://www.wacker.com>.

### Product data

Typical general characteristics	Inspection Method	Value
<b>Product data (uncured)</b>		
<b>Component A</b>		
Color		transparent
Viscosity at 23 °C	ISO 3219	1000 mPa s
Density at 23 °C		0,97 g/cm <sup>3</sup>
<b>Component B</b>		
Color		white
Viscosity at 23 °C	ISO 3219	1000 mPa s
Density at 23 °C		0,97 g/cm <sup>3</sup>
<b>Product data (catalyzed A + B)</b>		
Platinum-catalyst in component		B
Mix ratio	A : B	1 : 1
Viscosity of mix	ISO 3219	1000 mPa s
Pot life at 23 °C		60 min
<b>Product data (cured)</b>		
Color		white
Density at 23 °C	ISO 2781	0,97 g/cm <sup>3</sup>
Penetration (150 g hollow cone)	DIN ISO 2137	150 mm/10

Cured for 30 min at 150 °C in a circulating air oven.

These figures are only intended as a guide and should not be used in preparing specifications.

The data presented in this medium are in accordance with the present state of our knowledge but do not absolve the user from carefully checking all supplies immediately on receipt. We reserve the right to alter product constants within the scope of technical progress or new developments. The recommendations made in this medium should be checked by preliminary trials because of conditions during processing over which we have no control, especially where other companies' raw materials are also being used. The information provided by us does not absolve the user from the obligation of investigating the possibility of infringement of third parties' rights and, if necessary, clarifying the position. Recommendations for use do not constitute a warranty, either express or implied, of the fitness or suitability of the product for a particular purpose.

The management system has been certified according to DIN EN ISO 9001 and DIN EN ISO 14001

WACKER® is a trademark of Wacker Chemie AG. WACKER\_SilGel® is a trademark of Wacker Chemie AG.

For technical, quality, or product safety questions, please contact:

Wacker Chemie AG  
Hanns-Seidel-Platz 4  
81737 München, Germany  
[info.silicones@wacker.com](mailto:info.silicones@wacker.com)

[www.wacker.com](http://www.wacker.com)